



---

## **LensCoat® Sigma 300-800 INSTRUCTIONS**

### ***Piece 1 - Lens Hood Cover***

Remove the lens hood cover from the lens. Piece 1 has a ¼ inch hole at one end of the cover to accommodate for the lens hood locking knob. Carefully slide and stretch the lens cover into place without putting too much stress on the lock knob hole.

### ***Piece 2***

With the lens hood removed, stretch and slide piece 2 down from the glass to just below the focus rotating collar tapered side towards the camera

### ***Piece 3***

Carefully slide piece 3 down the lens just before the rotating lens collar.

### ***Piece 4***

Slide piece 4 down the lens aligning the focus distance scale. **For final placement, pull the distance scale window slightly away from the lens and adjust to the left or right.**

### ***Piece 5***

Carefully slide piece 5 down the lens just before the focus ring.

### ***Piece 6***

Slide on piece 6 by lining up the 1/8 hole to the lens mount mark and the hole for the AF/MF switch on the lens being careful not to pull/stretch the hole too much to prevent tears.

### ***Rotating Lens Collar***

The LensCoat® Sigma 300-800 lens cover kit includes 3 strips of neoprene with adhesive tape applied to the back. One is for the lens collar and the others can be used by the filter and above piece 5. Cut out the desired length for the parts of the lens collar you want to cover. Cut the longest piece first. After all the cutting is done then remove the adhesive tape backing by carefully folding back a small corner and apply to the lens collar.

LensCoat.com®  
80 Throckmorton Street  
Freehold, NJ 07728