



LensCoat® Sigma 120-300 OS INSTRUCTIONS

Piece 1- Lens Hood Cover

Remove the lens hood cover from the lens. Piece 1 has a hole at one end of the cover to accommodate for the lens hood locking knob. Carefully slide and stretch the lens cover into place without putting too much stress on the lock knob hole.

Remove the tripod mount foot from the rotating lens collar. This will allow for easy installation of pieces 2-5.

Piece 2

After removing the tripod mount foot slide piece 2 down below the zoom ring, tapered side towards the camera.

Piece 3

Slide piece 3 down onto the zoom ring.

Piece 4

Slide piece 4 down onto the focus ring.

Piece 5- Window piece

Slide piece 5 on by **carefully lining up the distance scale and OS windows and slide into place.. For final placement pull the distance scale window slightly away from the lens and adjust to the left or right.**

Piece 6

Slide on piece 6 by lining up the hole to the lens mount mark being careful not to pull/stretch the hole too much to prevent tears.

Rotating Lens Collar

The LensCoat® 120-300 OS lens cover kit includes one strip of neoprene with adhesive tape applied to the back. Cut out the desired length for the parts of the lens collar you want to cover. Cut the longest piece first. After all the cutting is done then remove the adhesive tape backing by carefully folding back a small corner and apply to the lens collar.

LensCoat.com®
80 Throckmorton Street
Freehold, NJ 07728