



LensCoat® Nikon 200-500 VR INSTRUCTIONS

Piece 1- Lens Hood Cover

Remove the lens hood cover from the lens. Carefully slide and stretch the lens cover into place.

Remove rotating collar for easy placement of pieces 2-7

Piece 2

With the rotating collar removed, stretch and slide piece 2 down to just above the zoom ring.

Piece 3

Slide piece 3 down to the zoom ring.

Piece 4

Carefully slide piece 4 down the lens just after the focus ring, lining up the hole for the zoom lock.

Piece 5

Carefully slide piece 5 down to the focus ring.

Piece 6

With rotating collar removed carefully slide piece 6 down the lens just after the rotating collar aligning the windows for the distance scale and AF/VR switches. **For final placement pull the windows slightly away from the lens and adjust to the left or right.**

Piece 7 (for use w/o the rotating collar)

If using without the rotating collar slide on piece 7 by aligning the hole for the alignment dot.

Rotating Lens Collar

The LensCoat® Nikon 200-500 lens cover kit includes a strip of neoprene with adhesive tape applied to the back for the rotating lens collar. Cutout the desired length for the parts of the lens collar you want to cover. Cut the longest piece first. After all the cutting is done then remove the adhesive tape backing by carefully folding back a small corner and apply to the lens collar.

Zoomed Lens Barrel

The LensCoat® Nikon 200-500 lens cover kit includes an optional piece that can be affixed to the lens via the Velcro strip **ONLY** when the lens is fully extended

LensCoat.com®
80 Throckmorton Street
Freehold, NJ 07728