



LensCoat® Sigma 100-400 INSTRUCTIONS

Piece 1- Lens Hood Cover

Remove the lens hood cover from the lens. Carefully slide and stretch the lens cover into place.

Piece 2

Stretch and slide piece 2 down the lens to the zoom ring.

Piece 3

Slide piece 3 down the lens to between the zoom and focus ring with the notch exposing the lock switch.

Piece 4

Slide piece 4 it down the lens to the focus ring.

Piece 5

Slide piece 5 on the last segment of the lens lining up the distance window and AF/OS controls. **For final placement pull the window for the slightly away from the lens and adjust to the left or right.**

Zoomed Lens Barrel

The LensCoat® Sigma 100-400 lens cover kit includes an optional piece that can be affixed to the lens via the Velcro strip used only when the lens is fully extended

LensCoat.com®
80 Throckmorton Street
Freehold, NJ 07728